







# ORDERING DETAILS

## **Glass Rack & Extender Combo**

Glass Racks and Extenders are available in a variety of combinations. Just select the compartment size you need and choose the color extender you want.

### **Individual Divided Extenders**

Want to simply update your current OptiClean Glass Racks with the color-coded option? You can order Divided Extenders separately in any of the six colors shown below.

**NOTE:** You may order the entire rack assembly in blue *or* choose to color code the extender(s) in one of the other five color options.

## SIX COLORS

Yellow 04 Combo 411 **Red 05** *Combo 410* 

Green 09 Combo 413 Orange 24 Combo 412 Lavender 89 Combo 414 Blue 14

## **OptiClean**™


Prod No	Description	Glass Dia**	Glass Height	Color	Pack	Cs Wt/ Cube					
Divided Extenders											
RE9C	9-Compartment Divided Extender	5.56"	1.5"	04, 05, 09, 24, 89	6 ea	9.60/2.77					
RE16C	16-Compartment Divided Extender	4.19"	1.5"	04, 05, 09, 24, 89	6 ea	10.75/2.77					
RE25C	25-Compartment Divided Extender	3.25"	1.5"	04, 05, 09, 24, 89	6 ea	12.15/2.77					
RE36C	36-Compartment Divided Extender	2.69"	1.5"	04, 05, 09, 24, 89	6 ea	13.35/2.77					
RE49C	49-Compartment Divided Extender	2.13"	1.5"	04, 05, 09, 24, 89	6 ea	14.90/2.77					
RE*	Open Extender	_	1.5"	14	6 ea	7.75/2.77					
9-Compa	9-Compartment Glass Rack - Compartment Size 5.81" Square										
RG9-1C <b>∆</b>	9-Compartment with 1 Extender	5.56"	4.75"	410, 411, 412, 413, 414	4 ea	23.65/5.80					
RG9-2C <b>△</b>	9-Compartment with 2 Extenders	5.56"	6.34"	410, 411, 412, 413, 414	3 ea	21.35/5.55					
RG9-3C △	9-Compartment with 3 Extenders	5.56"	7.94"	410, 411, 412, 413, 414	2 ea	18.00/4.54					
RG9-4C △	9-Compartment with 4 Extenders	5.56"	9.5"	410, 411, 412, 413, 414	2 ea	20.75/5.30					
RG9-5C <b>△</b>	9-Compartment with 5 Extenders	5.56"	11.1"	410, 411, 412, 413, 414	2 ea	28.10/6.12					
16-Comp	16-Compartment Glass Rack - Compartment Size 4.44" Square										
RG16-1C △	16-Compartment with 1 Extender	4.19"	4.75"	410, 411, 412, 413, 414	4 ea	25.60/5.42					
RG16-2C △	16-Compartment with 2 Extenders	4.19"	6.34"	410, 411, 412, 413, 414	3 ea	23.00/5.46					
RG16-3C △	16-Compartment with 3 Extenders	4.19"	7.94"	410, 411, 412, 413, 414	2 ea	19.30/4.48					
RG16-4C △	16-Compartment with 4 Extenders	4.19"	9.5"	410, 411, 412, 413, 414	2 ea	20.75/5.30					
RG16-5C <b>△</b>	16-Compartment with 5 Extenders	4.19"	11.1"	410, 411, 412, 413, 414	2 ea	28.10/6.12					
25-Comp	25-Compartment Glass Rack - Compartment Size 3.5" Square										
RG25-1C △	25-Compartment with 1 Extender	3.25"	4.75"	410, 411, 412, 413, 414	4 ea	29.30/5.58					
RG25-2C <b>△</b>	25-Compartment with 2 Extenders	3.25"	6.34"	410, 411, 412, 413, 414	3 ea	25.20/5.42					
RG25-3C △	25-Compartment with 3 Extenders	3.25"	7.94"	410, 411, 412, 413, 414	2 ea	21.10/4.51					
RG25-4C △	25-Compartment with 4 Extenders	3.25"	9.5"	410, 411, 412, 413, 414	2 ea	23.00/5.30					
RG25-5C △	25-Compartment with 5 Extenders	3.25"	11.1"	410, 411, 412, 413, 414	2 ea	28.10/6.12					
36-Comp	36-Compartment Glass Rack - Compartment Size 2.94" Square										
RG36-1C △	36-Compartment with 1 Extender	2.69"	4.75"	410, 411, 412, 413, 414	4 ea	31.80/5.58					
RG36-2C <b>△</b>	36-Compartment with 2 Extenders	2.69"	6.34"	410, 411, 412, 413, 414	3 ea	27.10/5.46					
RG36-3C △	36-Compartment with 3 Extenders	2.69"	7.94"	410, 411, 412, 413, 414	2 ea	22.70/4.45					
RG36-4C △	36-Compartment with 4 Extenders	2.69"	9.5"	410, 411, 412, 413, 414	2 ea	26.00/5.30					
RG36-5C <b>△</b>	36-Compartment with 5 Extenders	2.69"	11.1"	410, 411, 412, 413, 414	2 ea	28.10/6.12					
49-Comp	49-Compartment Glass Rack - Compartment Size 2.38" Square										
RG49-1C △	49-Compartment with 1 Extender	2.13"	4.75"	410, 411, 412, 413, 414	4 ea	31.30/5.80					
RG49-2C <b>△</b>	49-Compartment with 2 Extenders	2.13"	6.34"	410, 411, 412, 413, 414	3 ea	31.50/5.55					
RG49-3C <b>△</b>	49-Compartment with 3 Extenders	2.13"	7.94"	410, 411, 412, 413, 414	2 ea	23.20/4.45					
RG49-4C △	49-Compartment with 4 Extenders	2.13"	9.5"	410, 411, 412, 413, 414	2 ea	20.75/5.30					
RG49-5C <b>△</b>	49-Compartment with 5 Extenders	2.13"	11.1"	410, 411, 412, 413, 414	2 ea	20.75/5.30					

# OptiClean™ NeWave™

Prod No	Description	Glass Dia**	Glass Height	Color	Pack	Cs Wt/ Cube				
Divided Extenders										
REW20SC	20-Compartment Extender	3.56"	1.5"	04, 05, 09, 24, 89	6 ea	13.90/2.77				
REW30SC	30-Compartment Extender	2.88"	1.5"	04, 05, 09, 24, 89	6 ea	15.60/2.77				
20-Compartment NeWave Glass Rack - Compartment Size 3.81" Dia										
RW20-C △	20-Compartment with Integrated Extender	3.56"	4.75"	410, 411, 412, 413, 414	4 ea	28.90/1.35				
RW20-1C △	20-Compartment with 2 Extenders	3.56"	6.34"	410, 411, 412, 413, 414	3 ea	28.70/5.46				
RW20-2C △	20-Compartment with 3 Extenders	3.56"	7.94"	410, 411, 412, 413, 414	2 ea	22.00/4.48				
RW20-3C △	20-Compartment with 4 Extenders	3.56"	9.5"	410, 411, 412, 413, 414	2 ea	25.60/5.30				
RW20-4C △	20-Compartment with 5 Extenders	3.56"	11.1"	410, 411, 412, 413, 414	1 ea	27.92/6.12				
30-Compartment NeWave Glass Rack - Compartment Size 3.13" Dia										
RW30-C △	30-Compartment with Integrated Extender	2.88"	4.75"	410, 411, 412, 413, 414	4 ea	31.80/1.35				
RW30-1C △	30-Compartment with 2 Extenders	2.88"	6.34"	410, 411, 412, 413, 414	3 ea	31.70/5.46				
RW30-2C △	30-Compartment with 3 Extenders	2.88"	7.94"	410, 411, 412, 413, 414	2 ea	24.00/4.48				
RW30-3C △	30-Compartment with 4 Extenders	2.88"	9.5"	410, 411, 412, 413, 414	2 ea	26.70/5.30				
RW30-4C △	30-Compartment with 5 Extenders	2.88"	11.1"	410, 411, 412, 413, 414	1 ea	29.30/6.12				

NSF Listed products are designated with a △

#### Combination Rack & Extender Color Codes



For complete listings see our full catalog or visit www.carlislefsp.com/findrack



©2015 Carlisle FoodService Products Oklahoma City, OK 73131 www.carlislefsp.com | 800.654.8210

**LCCGRFLYR** 

**Connect with Carlisle!** 









<sup>\*</sup> Note: The RE Open Extender can be used with any OptiClean Glass or Dish Rack

<sup>\*\*</sup> Dimensions shown are for the recommended maximum glass size for the compartment